# Technical Datasheet Vitralit® 1600 LV



#### **Product Description**

Panacol Vitralit<sup>®</sup> adhesives are one-component, solvent-free radiation-curing adhesives. The advantages are very short curing times, good adhesion to a variety of substrates, and easy handling. Vitralit<sup>®</sup> products are used in electronics, medical applications, optics and for fixing parts in general.

Vitralit<sup>®</sup> 1600 LV is a UV-curable epoxy resin which has been specially developed for use in electronics and electrical engineering as glob-top. As a special feature, Vitralit<sup>®</sup> 1600 LV has a thermal initiator, which allows subsequent curing of shadow areas. Vitralit<sup>®</sup> 1600 LV is characterized by a high glass transition temperature, low water absorption and a low ion content (Na + <5ppm, K + <5ppm, Cl- <5ppm) and is thus suitable for semiconductors.

### **Curing Properties**

UV-A	VIS	Thermal curing	Activator curing
✓	-	✓	-

<sup>✓</sup> suitable - not suitable

The product cures within seconds with radiation in the UV-A - range (320 nm - 390 nm). For rapid and high quality crosslinking we recommend the UV devices manufactured by Dr. Hoenle AG, which complement our adhesive technology.

Bluepoint LED/LED-spot			
Wavelength [nm] 365 405			
Suitability	++	-	

<sup>+</sup> application-related ++ well-suited +++ ideal - not suitable

To obtain full cure at least one substrate must be transparent to the recommended wavelength. The curing speed will depend on the intensity of light, light source, the exposure time, and the light transmittance of the substrate. Increased mechanical properties are achieved after 24 hours.

UV-curing			
Intensity [mW/cm²]	Layer thickness [mm]	Time [sec]	
60	0,5	30	

Thermal curing	[min]
Time at 105°C	30

#### **Technical Data**

 Resin
 epoxy

 Appearance
 grey

 Filler
 quartz

 Filler – weight [%]
 52

 Particle size D95 [nm]
 32

## Technical Datasheet

## Vitralit® 1600 LV



### **Uncured material**

Viscosity [mPas] (Brookfield LVT, 25°C, Sp 4, 30rpm) PE-Norm 001	5 000 - 6 000
Density [g/cm³] PE-Norm 004	1,43
Flash point [°C] PE-Norm 050	> 100

### **Cured material**

Hardness shore D PE-Norm 006	83 - 93
Temperature resistance [°C] PE-Norm 065	-40 - 180
Shrinkage [%] PE-Norm 031	0,4
Water absorption [mass %] PE-Norm 016	<0,25

Glass transition temperature DSC [°C] PE-Norm 009	150
Coefficient of linear expansion [ppm/K] below Tg PE-Norm 017	40,0

Thermal conductivity [W/m*K] PE-Norm 062	0,8
Dielectric constant [10kHz]	3,4
Dielectric strength [kV/mm]	35,2

Young's modulus E [MPa] PE-Norm 056	5 780
Tensile strength [MPa] PE-Norm 014	37
Elongation at break [%] PE-Norm 014	1

### Transport/Storage/Shelf Life

Trading unit	Transport	Storage	Shelf-life*
Cartridge	0°C - 10°C	-20°C - 0°C	at delivery min. 6 months
Other packages		0°C - 10°C	max. 12 months

<sup>\*</sup>Store in original, unopened containers!

# Technical Datasheet Vitralit® 1600 LV



#### **Instructions for Use**

#### **Surface preparation**

The surfaces to be bonded should be free of dust, oil, grease or other dirt in order to obtain an optimal and reproducible bond.

For cleaning we recommend the cleaner IP<sup>®</sup> Panacol. Substrates with low surface energy (e.g. polyethylene, polypropylene) must be pretreated in order to achieve sufficient adhesion.

#### Application

Our products are supplied ready to use. Depending on packaging they can be applied by hand directly from the container or semi or fully automatically. With automated application from the cartridge the adhesive is conveyed by a compressed air-operated displacement plunger via a valve in the needle. When metering low viscosity materials from bottles the adhesive is transported by a diaphragm valve. If help is required, please contact our application engineering department.

Adhesive and substrate may not be cold and must be warmed up to room temperature prior to processing.

After application, bonding of the parts should be done quickly. Vitralit<sup>®</sup> adhesives cure slowly in daylight. Therefore, we recommend to expose the material to as little light as possible and the use of opaque hose lines and dispensing needles.

For safety information refer to our safety data sheet.

#### Note

The product is free of heavy metals, PFOS and Phthalates and is conform to the EU-Directive 2011/65/EU "RoHS II".

Our data sheets have been compiled to the best of our knowledge. The enclosed information describes characteristic properties, with no declaration of commitment. We recommend trials in order to confirm that our products satisfy the particular application requirements. For any additional technical support, please contact our application engineering department. For warranty claims, please refer to our standard terms and conditions.